

**Product Details**

**Q2334V 'P' Trapped Gully Assembly**

**Technical Data**



**Dimensions:**

223 square at finish level  
185 dia. body  
256 - Height below Body Flange  
65 to 90 - min/max height between FFL and body flange  
112 - depth body flange to outlet center line

**Connection** - 110mm Plastic, 100mm DIN19522 / 4" BS416 / Harmer SML

**Free Area** - 60cm<sup>2</sup>

**Materials** - Stainless steel

**Weight** - 6.4 kg

**General Description:**

223 Square Stainless Steel Q series 'P' Trapped Gully Assembly, for use with flexible sheet floor covering (eg. vinyl) (Height Adjustable plus Optional Side Inlets and Optional Grade 316), with 110.2 dia. Horizontal outlet.

**Options:**

To specify an option, add option letter(s) as a suffix to the Spec. Code

B - filter bucket

M - grade 316 stainless steel

N - non trapped version (supplied without bell trap assembly)

**Materials:**

**Stainless Steel - Austenitic Grade 304 (Grade 316 optional on most products):** Used for bodies, gratings, funnels, access covers, filter buckets and fixings. A corrosion-resistant metal containing significant amounts of nickel and chromium; AISI grade 304 stainless steel is used as standard, which is suitable for general use in and around buildings including most coastal locations. In applications such as swimming pools or having an aggressive atmosphere, grade 316 is recommended and is available optionally (if available, code 'M' will be listed under 'Options'). An even higher grade may be required for applications in highly corrosive environments including where exposure to seawater may be anticipated. Clean with soap and warm water rinse and wipe dry. Gratings may also be cleaned in certain dishwashers. Under no circumstances treat with metal scouring pads, metal scrapers or wire wool as these will contaminate surfaces leaving rust spots. Take care to cover stainless steel items when site work is going on, to avoid contamination with rust-inducing particles such as when mild steel or cast iron items are being cut.

All dimensions are in millimetres unless stated. In line with general practice all dimensions shown are nominal.

Wade International

Third Avenue, Halstead, Essex, CO9 2SX.

Telephone: +44 (0)1787 475151

Fax: +44 (0)1787 475579

e-mail: [wadetech@alumascwms.co.uk](mailto:wadetech@alumascwms.co.uk)

website: <https://www.alumascwms.co.uk/brands/wade/>

**Dimensioned Section for Q2334V:**

